

Side Doors, DNS



A side door mounted on an enclosure allows easy access to the rear part of components mounted in the front when access from the back is not possible.

FEATURES

Description: Instead of the side panel SPM. For easy access to the equipment inside the enclosure or when enclosures are mounted rear to rear. Equipped with standard double-bit 3 mm lock which makes all lock options possible. Door frame optional.

Material: 2 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 10.

Pack quantity: 1 door including mounting frame.

SPECIFICATIONS

- Thickness:

2mm
- Color:

Light Gray
- Material:

Mild Steel
- Finish:

Powder Coated
- Color Code:

RAL 7035

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Enclosure Material	Product Family
DNS2005R5	DNS2005R5	1982mm	493mm	51mm	Mild Steel	Free-Standing
DNS1805R5	DNS1805R5	1782mm	493mm	51mm	Mild Steel	Free-Standing
DNS1806R5	DNS1806R5	1782mm	593mm	51mm	Mild Steel	Free-Standing
DNS2006R5	DNS2006R5	1982mm	593mm	51mm	Mild Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE