

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Power Utilities

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFICATIONS



FEATURES

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Shock and Vibration Tolerance
24567-161	3 U	175 mm	1	Backplane	160 mm	5 g (force)
24567-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)
24567-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	5 g (force)
24567-461	6 U	175 mm	1	Backplane	160 mm	5 g (force)
24567-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	5 g (force)
24567-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	5 g (force)
24567-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	5 g (force)

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24567-161	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-162	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-163	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-164	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-461	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-462	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

CatalogNumber	HandleIncluded	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24567-463	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24567-464	Yes	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load	Certifications
24567-161	15 kgf	RoHS
24567-162	15 kgf	RoHS, DB
24567-163	15 kgf	RoHS, DB
24567-164	15 kgf	RoHS, DB
24567-461	15 kgf	RoHS, DB
24567-462	15 kgf	RoHS, DB
24567-463	15 kgf	RoHS, DB
24567-464	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE