

# Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

## Power Utilities

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

### FEATURES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Complies With               |
|----------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-876      | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-877      | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-878      | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-879      | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-880      | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-881      | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |
| 21630-882      | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Complies With               |
|---------------|-------------|---------|--------|------------|------------|-----------------------------|
| 21630-883     | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-2 |

Table 2/2

| Catalog Number | Locking Type    | Material | Product Type | Protection Rating | Type                   | Works With  |
|----------------|-----------------|----------|--------------|-------------------|------------------------|-------------|
| 21630-876      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-877      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-878      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-879      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-880      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-881      | 4-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-882      | 5-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |
| 21630-883      | 5-Point Locking | Steel    | Cabinet Door | IP20              | Steel Door, Perforated | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**