

# EuropacPRO Advanced EMC Side Panel Covers for C-Profile Adaptors



Aluminium Side panel 3 mm to increase the EMC shielding effect of the subrack by increasing the material thickness and covering the not needed cut-outs. In this version specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet.

## FEATURES

Side panel covers for increased lateral RF shielding, specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet

Assembled on the outside of the standard side panel

Assembly material included

Compatible C-profile adaptors can be found in the recommended accessory section

## SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Product Family | Type   | Rack Height | Depth | EMC Shielding |
|----------------|--------------|----------------|--------|-------------|-------|---------------|
| 24563-355      | Side Panel   | EuropacPRO     | Type H | 3U          | 175mm | Yes           |
| 24563-356      | Side Panel   | EuropacPRO     | Type H | 3U          | 235mm | Yes           |
| 24563-359      | Side Panel   | EuropacPRO     | Type H | 3U          | 295mm | Yes           |
| 24563-360      | Side Panel   | EuropacPRO     | Type H | 3U          | 355mm | Yes           |
| 24563-361      | Side Panel   | EuropacPRO     | Type H | 3U          | 415mm | Yes           |
| 24563-362      | Side Panel   | EuropacPRO     | Type H | 3U          | 495mm | Yes           |
| 24563-375      | Side Panel   | EuropacPRO     | Type H | 6U          | 175mm | Yes           |

| CatalogNumber | Product Type | Product Family | Type   | Rack Height | Depth | EMC Shielding |
|---------------|--------------|----------------|--------|-------------|-------|---------------|
| 24563-376     | Side Panel   | EuropacPRO     | Type H | 6U          | 235mm | Yes           |
| 24563-379     | Side Panel   | EuropacPRO     | Type H | 6U          | 295mm | Yes           |
| 24563-380     | Side Panel   | EuropacPRO     | Type H | 6U          | 355mm | Yes           |
| 24563-381     | Side Panel   | EuropacPRO     | Type H | 6U          | 415mm | Yes           |
| 24563-382     | Side Panel   | EuropacPRO     | Type H | 6U          | 495mm | Yes           |

Table 2/2

| Catalog Number | Length | Material | Finish     | Package Quantity | Package Unit | Quick Ship |
|----------------|--------|----------|------------|------------------|--------------|------------|
| 24563-355      | 175mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-356      | 235mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-359      | 295mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-360      | 355mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-361      | 415mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-362      | 495mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-375      | 175mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-376      | 235mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-379      | 295mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-380      | 355mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-381      | 415mm  | Aluminum | Passivated | 2                | Pair         | No         |
| 24563-382      | 495mm  | Aluminum | Passivated | 2                | Pair         | No         |

ADDITIONAL PRODUCT DETAILS

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

Versions besides 3 and 6 U available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE