

nVent CADDY Cat HP J-Hook with Z Purlin Clip, Swivel, 75 mm dia, 1.5–2.5 mm Flange


Data Solutions

CATALOG NUMBER

CAT48HP123



CERTIFICATIONS



FEATURES

Requires only a hammer to install

Rotates 360 degrees to support various directional runs of cable

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

PRODUCT ATTRIBUTES


Article Number: 181265
Material: Steel; Spring Steel
Finish: Pregalvanized; nVent CADDY Armour
Diameter (Ø): 75mm
Area: 5974mm²
Cable Capacity, Cat 5e: 200
Cable Capacity, Cat 6: 150
Cable Capacity, Cat 6A: 80
Flange Thickness (FT): 1.5 – 2.5mm
Static Load: 270N

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE