

Hammer Die

Data Solutions



FEATURES

Hardened steel die

Used to form the end of a field-made bond

Formed end designed to fit specific nVent ERICO Cadweld mold

SPECIFICATIONS

Material: Steel

Table 1/1

Catalog Number	Article Number	Type	Conductor Size	nVent ERICO Sleeve
JD05		Grounding	1/0 Concentric	S05F
WD80		Power	1/0 Concentric	S05F
WD84		Power	2/0 Concentric, 1/0 Ropelay	S03F
JD03		Grounding	2/0 Concentric	S03F
JD06		Grounding	2/0 Ropelay	S06F

Catalog Number	Article Number	Type	Conductor Size	nVent ERICO Sleeve
WD85		Power	2/0 Ropelay	S06F
SBD50		Signal	3/16" Bondstrand	SBS12C
JD01		Grounding	4/0 Concentric	S01F
WD82		Power	95 mm ² Concentric, 4/0 Concentric	S01F
JD02		Grounding	4/0 Ropelay	S02F
WD83		Power	4/0 Ropelay	S02F
WD88		Power	4/0 Welding cable	S429F3N16
SBD51		Signal	5/16" Bondstrand	SBS09C
SBD55		Signal	35 mm ² Concentric	S17F
WD94		Power	35 mm ² Concentric	S17F
PBWD102	184200	Power	120 mm ² Concentric	H106F
PBWD104		Power	145 mm ² Concentric	S429F3N16
WD87		Power	150 mm ² Ropelay	S24F
PBWD106	184090	Power	240 mm ² Concentric	S429FY922
WD105		Power	240 mm ² Concentric	S429FY922
PBWD99		Power	240 mm ² Ropelay	S429F3N16
JD07		Grounding	250 kcmil Ropelay	S07F
WD79		Power	500 kcmil Ropelay	S429F3S20

Catalog Number	Article Number	Type	Conductor Size	nVent ERICO Sleeve
JD09		Grounding	#2 Concentric	S09F
JD11		Grounding	#4 Concentric	S20F

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE