

# ProLine Pagoda Exhaust Vents

## Data Solutions

Pagoda Exhaust Vents can be field-installed on any ProLine or ProLine G2 solid top to provide active enclosure cooling.



### FEATURES

Axial fan and finger guard mounted in housing

Drip-protected, raised cover is removable from the inside of the enclosure

115V or 230V versions with lead wires

115V power cord option

Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1

Includes gasket and mounting hardware

### SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material   | Voltage AC | Color      | Color Code | Finish        |
|----------------|----------------|------------|------------|------------|------------|---------------|
| PPT1C          | 11095          | Mild Steel | 115V       | Light Gray | RAL 7035   | Powder Coated |

Table 2/2

| Catalog Number | Article Number | Thickness |
|----------------|----------------|-----------|
| PPT1C          | 11095          | 1.9mm     |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**