

## CABS Hardware Kit, UL®



### CERTIFICATIONS



### FEATURES

Kit includes 4 threaded rods, 4 inserts, 2 screws, 10 nuts, 6 spacers and sleeve

Multiple rod lengths available to accommodate various busbar widths and profile configurations

Threaded rods are made from non-magnetic stainless steel to reduce the magnetic loop between phases

Insulator sleeves allow for minimal space between phases

Robust hardware provides strength and rigidity

Installs quickly and easily

Time-savings and lower total install costs compared to traditional methods

Engineered and standardized design

RoHS compliant

### SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Stainless Steel 316 (EN 1.4401);Steel;Polyolefin

Table 1/1

| Catalog Number | Article Number | Rod Length | Thread Size | Unit Weight |
|----------------|----------------|------------|-------------|-------------|
|----------------|----------------|------------|-------------|-------------|

|            |        |       |     |         |
|------------|--------|-------|-----|---------|
| CABS140HWT | 549526 | 140mm | M10 | 0.27 kg |
| CABS220HWT | 549528 | 220mm | M10 | 0.3 kg  |
| CABS190HWT | 549527 | 190mm | M10 | 0.3 kg  |

## ADDITIONAL PRODUCT DETAILS

Threaded rods must be installed on both sides of each phase.

| Busbar Width | Single Profile Support | Double Profile Support |
|--------------|------------------------|------------------------|
| 50.8 mm      | CABS140HWT             | CABS140HWT             |
| 63.5 mm      |                        | CABS190HWT             |
| 76.2 mm      |                        |                        |
| 101.6 mm     | CABS190HWT             |                        |
| 127.0 mm     |                        |                        |
| 152.4 mm     | CABS240HWT             | CABS240HWT             |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**