

APO Non-Metallic Mounting Feet

APO Mounting Feet allows APO enclosure mounting to any vertical surface supporting the load of the enclosure.



FEATURES

Set of four pieces

For heavy duty mounting

The brackets are mounted directly to the rear of the box in provided reinforcements

M4 threaded inserts are provided for secure attachment

Maximum load cannot exceed 330lbs (150kg)

SPECIFICATIONS

Table 1/1					
Catalog Number	Article Number	Material	Finish	Color	Quick Ship
41525.050	41525.050	Polyamide	Smooth Matte	Black	No
AP-MFSS	AP-MFSS	Stainless Steel	Mill		No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE