

## Cable Entry Cabinets



Cable Entry Cabinets facilitate cable entry into the sides of enclosures. Open top and bottom of cabinet provide cable access and a means for managing cable. Closure plates, available as optional accessories, seal the open ends of the cabinet. Front opening of cabinet can be closed with either hinged solid door or screw-on solid cover. Cabinets have foam-in-place gasket and optional accessories to maintain enclosure environmental integrity.

### FEATURES

---

14 gauge (1.75mm) mild steel

RAL 7035 textured light-gray polyester powder paint finish

Foam-in-place gasket and optional accessories to maintain environmental integrity

Open top and bottom of cabinet; closure plates sold separately

Front opening of cabinet can be closed with either solid door or cover

## SPECIFICATIONS

---

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
PCE165300	34189	1600mm	500mm	299mm	1.9mm	No
PCE166300	34199	1600mm	600mm	299mm	1.9mm	No
PCE168300	34209	1600mm	800mm	299mm	1.9mm	No
PCE186300	34229	1800mm	600mm	299mm	1.9mm	No
PCE188300	34239	1800mm	800mm	299mm	1.9mm	No
PCE205300	34249	2000mm	500mm	299mm	1.9mm	No
PCE206300	34259	2000mm	600mm	299mm	1.9mm	No
PCE208300	34269	2000mm	800mm	299mm	1.9mm	No
PCE225300	34279	2200mm	500mm	299mm	1.9mm	No
PCE228300	34299	2200mm	800mm	299mm	1.9mm	No

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**