

# CS480 Swivel Base Internal



CS480 Swivel Base Internal allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 340 degrees. Base mounting hardware is hidden. Maintenance-free bearings.

## INDUSTRY STANDARDS

---

IEC 60529, IP66

## FEATURES

---

Base can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket is included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Finish
CCSS48BBRI	42489	110mm	116mm	116mm	Stainless Steel 304	Brushed

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**