

Elbow 45-Degree Feed-Through



Feed-Through 45-Degree Elbows are used for continuous runs with 45-degree turns. Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Feed-Through 45-Degree Elbows are used for continuous runs with 45-degree turns

Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F22WE45	14080	Elbow	64mm	64mm	1.9mm	No
F44WE45	14270	Elbow	102mm	102mm	1.9mm	No
F66WE45	14480	Elbow	152mm	152mm	1.9mm	No
F88WE45	14690	Elbow	203mm	203mm	1.9mm	No

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints. Dimension J is from intersection of center lines.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE