

# Concept Deep Hinged Window Kit Type 12, fits 310x360mm, Gray, Steel

## CATALOG NUMBER

**CWHD3136**



Concept deep hinged window kit can be used as an accessory window kit on larger standard nVent HOFFMAN enclosure doors. It provides two-inch space between enclosure front opening and window surface, accommodating switches, lights, meters and other components.

## INDUSTRY STANDARDS

UL 508A, 508, File Number E61997: Type 12

NEMA Type 12

IEC 60529, IP66

## FEATURES

Hinged on the left side and has a single-point slotted latch

Optional locking or non-locking wing knob latch is available

Aesthetic die-cast aluminum frame

0.188-in. (5-mm) thick, clear polycarbonate window

## PRODUCT ATTRIBUTES

Article Number: 41690

Product Family: Concept

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 1.52mm

Window Size: 253 x 276mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**