

Utility Junction (UJ) Cabinet



Utility Junction (UJ) Cabinet provides sectionalizing and tap-point functionality for underground distribution systems. Available in a wide variety of single- and three-phase models, these enclosures are rated 15 and 25 KV at 200 or 600 amperes and will accept two-, three- and four-way junctions from all manufacturers.

INDUSTRY STANDARDS

RUS Approved

ANSI C57.12.28 Pad-Mounted Equipment Enclosure Integrity

FEATURES

Recessed stainless steel penta-head bolt with padlock security system standard on all models

5/8-11 threaded lifting provisions

Wind stop standard on all models (two stops provided if B dimension is greater than or equal to 42-inch (1067mm))

Ground nut for each phase

Full range of modifications available on request

When ordering UJ cabinets, customer may specify multiple mounting panel options, including mild steel, galvanized and stainless steel (panels must be purchased separately)

ANSI C57.12.28 Pad-Mounted Equipment Enclosure Integrity RUS Approved

SPECIFICATIONS

Finish: Powder Coated

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Color
UJ303018A	17936	762mm	762mm	457mm	Aluminum	Munsell Green
UJ303018M2	16908	762mm	762mm	457mm	Mild Steel	Munsell Green
UJ303019M2	16911	762mm	762mm	483mm	Mild Steel	Munsell Green
UJ303023M2	16912	762mm	762mm	584mm	Mild Steel	Munsell Green
UJ303024M2	16973	762mm	762mm	610mm	Mild Steel	Munsell Green
UJ306424M2	16914	762mm	1626mm	610mm	Mild Steel	Munsell Green
UJ306623M2	16915	762mm	1676mm	584mm	Mild Steel	Munsell Green
UJ482618M2	16917	1219mm	660mm	457mm	Mild Steel	Munsell Green
UJP1G	17945	296mm	470mm		Mild Steel	White
UJP1GOFF	17947	296mm	470mm		Mild Steel	White
UJP1M	17941	296mm	470mm		Mild Steel	White
UJP1MOFF	17943	296mm	470mm		Mild Steel	White
UJP1SS	17951	296mm	470mm		Stainless Steel 304	White
UJP1SSOFF	17953	296mm	470mm		Stainless Steel 304	White
UJ304824M2	16974	762mm	1219mm	610mm	Mild Steel	Munsell Green
UJP2G	17946	296mm	546mm		Mild Steel	White
UJP2GOFF	17948	296mm	546mm		Mild Steel	White
UJP2M	17942	296mm	546mm		Mild Steel	White

Catalog Number	Article Number	Height	Width	Depth	Material	Color
UJP2MOFF	17944	296mm	546mm		Mild Steel	White
UJP2SS	17952	296mm	546mm		Stainless Steel 304	White
UJP2SSOFF	17954	296mm	546mm		Stainless Steel 304	White
UJ306018M2	16913	762mm	1524mm	457mm	Mild Steel	Munsell Green
UJ306724M2	16976	762mm	1702mm	610mm	Mild Steel	Munsell Green
UJ307424M2	16975	762mm	1880mm	610mm	Mild Steel	Munsell Green
UJ307622M2	16916	762mm	1930mm	559mm	Mild Steel	Munsell Green
UJ306018A	17937	762mm	1524mm	457mm	Aluminum	Munsell Green
UJ306723A	17938	762mm	1702mm	584mm	Aluminum	Munsell Green

ADDITIONAL PRODUCT DETAILS

UJ303018A, UJ306018A and UJ306723A aluminum models are .125-inch (3.3mm) thick.

Catalog weights and dimensions are careful estimates but not guaranteed.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE