

# RackPower PDU, RP1xxx, 230 VAC, 1-phase

## Power Utilities

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

### FEATURES

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Connecting cable 3 m, with IEC 60309 332P6 connector

C13, C19 outlets

### SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Socket Type      | Color | Length  | Voltage AC | Function        |
|----------------|--------------|------------------|-------|---------|------------|-----------------|
| RP1325         | Socket Strip | IEC C13, IEC C19 | Black | 1490 mm | 230 V      | Input Monitored |

Table 2/2

| Catalog Number | Depth | Width |
|----------------|-------|-------|
| RP1325         | 53 mm | 52 mm |

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**