

# Frame Type Plug-In Unit PRO Kit, Perforated Covers, 1 Connector, 6 U, 28 HP, 167 mm

## CATALOG NUMBER

**24812-728**



Frame type plug-in unit, non-shielded, perforated top / bottom cover, rear panel with cutout for one connector.

## CERTIFICATIONS



## FEATURES

---

- Extruded side panels right and left, with grooves for insertion of a printed circuit board (standard board position is on the left only)
- Rear panel with cut-out for single connector (conforms to EN 60603, DIN 41612, construction types: B, C, D, F, H, Q, R, S)
- Cover plate with perforation, for guide rails (airflow approx. 60%); please order guide rails separately

## PRODUCT ATTRIBUTES

---

|                                                                |
|----------------------------------------------------------------|
| Rack Height: 6U                                                |
| Rack Width: 28HP                                               |
| Package Quantity: 1                                            |
| Handle Type: Trapezoid                                         |
| Rear Panel Type: Single Connector Cut-Out                      |
| Cover Plate Type: Cover Plate with Perforation for Guide Rails |
| Front Finish: Anodized                                         |
| Rear Finish: Anodized                                          |
| Cooling: Perforated                                            |
| Depth (D): 167mm                                               |
| EMC Shielding: No                                              |
| Finish: Anodized                                               |
| Material: Aluminum                                             |
| Product Type: Cassette                                         |
| Type: Frame Type Plug-in Units PRO                             |
| Net Weight: 1.4kg                                              |

## ADDITIONAL PRODUCT DETAILS

---

To fit further boards without rear connector, guide rail (part no. 24812-301) and 'Board fixing from slot 2' (part no. 24812-301 + screw part no. 24560-178) are required, 2 guide rails, 2 rear panel holders and board fixing for slot 1 and one slot 2 are already included.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**