nVent | ERIFLEX

We connect and protect

HFBT nVent ERIFLEX Flexibar Bending Tool

CATALOG NUMBER

HFBT

CERTIFICATIONS

RoHS

FEATURES

- Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation
- Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation
- Portable tool can be used on the jobsite or attached to a workbench
- Includes tool box

PRODUCT ATTRIBUTES

- Article Number: 558920
- Material: Steel
- Bending Radius: 10mm
- Bending Angle: 180 ° Max
- Depth: 120mm
- Height: 215 mm
- Width: 345 mm
- Unit Weight: 7 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.