

# Front Panel, Anodized, Unshielded, Screw Assembly

## Power Utilities

Anodized front panel, unshielded version, Al, 2.5 mm.



### CERTIFICATIONS



### FEATURES

Partial width front panel, Al, 2.5 mm

Al, anodized

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish |
|----------------|-------------|------------|------------------|----------------|--------------|-------------|
| 30807-596      | 4 U         | 84 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30808-067      | 3 U         | 63 HP      | 1                | Screw-on Front | Anodized     | Anodized    |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish |
|---------------|-------------|------------|------------------|----------------|--------------|-------------|
| 30807-764     | 6 U         | 42 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30807-494     | 3 U         | 42 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30807-771     | 6 U         | 63 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30807-776     | 6 U         | 84 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30807-506     | 3 U         | 84 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30807-416     | 2 U         | 84 HP      | 1                | Screw-on Front | Anodized     | Anodized    |
| 30818-741     | 6 U         | 2 HP       | 5                | Screw-on Front | Anodized     | Conductive  |
| 30810-432     | 3 U         | 2 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-501     | 3 U         | 14 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-510     | 3 U         | 5 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-509     | 3 U         | 7 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-508     | 3 U         | 3 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-482     | 3 U         | 6 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-483     | 3 U         | 10 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-496     | 3 U         | 28 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-487     | 3 U         | 21 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-485     | 3 U         | 12 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-484     | 3 U         | 8 HP       | 5                | Screw-on Front | Anodized     | Anodized    |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish |
|---------------|-------------|------------|------------------|----------------|--------------|-------------|
| 30807-481     | 3 U         | 4 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-778     | 6 U         | 4 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-777     | 6 U         | 5 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-779     | 6 U         | 8 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-752     | 6 U         | 6 HP       | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-780     | 6 U         | 16 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-766     | 6 U         | 28 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-758     | 6 U         | 14 HP      | 5                | Screw-on Front | Anodized     | Conductive  |
| 30807-757     | 6 U         | 21 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-755     | 6 U         | 12 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-753     | 6 U         | 10 HP      | 5                | Screw-on Front | Anodized     | Anodized    |
| 30807-833     | 6 U         | 7 HP       |                  | Screw-on Front | Anodized     | Anodized    |

Table 2/3

| Catalog Number | Treated Edges | Complies With                   | EMC Shielding | Height   | Material | Product Type |
|----------------|---------------|---------------------------------|---------------|----------|----------|--------------|
| 30807-596      | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 172.9 mm | Aluminum | Front Panel  |
| 30808-067      | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-764      | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |

| CatalogNumber | Treated Edges | Complies With                   | EMC Shielding | Height   | Material | Product Type |
|---------------|---------------|---------------------------------|---------------|----------|----------|--------------|
| 30807-494     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-771     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-776     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-506     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-416     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 84 mm    | Aluminum | Front Panel  |
| 30818-741     | No            | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30810-432     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-501     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-510     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-509     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-508     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-482     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-483     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-496     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-487     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |

| CatalogNumber | Treated Edges | Complies With                   | EMC Shielding | Height   | Material | Product Type |
|---------------|---------------|---------------------------------|---------------|----------|----------|--------------|
| 30807-485     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-484     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-481     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  |
| 30807-778     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-777     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-779     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-752     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-780     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-766     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-758     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-757     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-755     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-753     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |
| 30807-833     | Yes           | IEC 60297-3-101, IEEE 1101.1/10 | No            | 261.8 mm | Aluminum | Front Panel  |

Table 3/3

| Catalog Number | Type | Width | Certifications |
|----------------|------|-------|----------------|
|----------------|------|-------|----------------|

|           |                            |          |      |
|-----------|----------------------------|----------|------|
| 30807-596 | Front Panel without Handle | 426.4 mm |      |
| 30808-067 | Front Panel without Handle | 319.7 mm | RoHS |
| 30807-764 | Front Panel without Handle | 213 mm   | RoHS |
| 30807-494 | Front Panel without Handle | 213 mm   | RoHS |
| 30807-771 | Front Panel without Handle | 319.7 mm | RoHS |
| 30807-776 | Front Panel without Handle | 426.4 mm | RoHS |
| 30807-506 | Front Panel without Handle | 426.4 mm | RoHS |
| 30807-416 | Front Panel without Handle | 426.4 mm | RoHS |
| 30818-741 | Front Panel without Handle | 9.8 mm   | RoHS |
| 30810-432 | Front Panel without Handle | 9.8 mm   | RoHS |
| 30807-501 | Front Panel without Handle | 70.8 mm  | RoHS |
| 30807-510 | Front Panel without Handle | 25 mm    | RoHS |
| 30807-509 | Front Panel without Handle | 35.2 mm  | RoHS |
| 30807-508 | Front Panel without Handle | 14.9 mm  | RoHS |
| 30807-482 | Front Panel without Handle | 30.1 mm  | RoHS |
| 30807-483 | Front Panel without Handle | 50.5 mm  | RoHS |
| 30807-496 | Front Panel without Handle | 141.9 mm | RoHS |
| 30807-487 | Front Panel without Handle | 106.3 mm | RoHS |
| 30807-485 | Front Panel without Handle | 60.6 mm  | RoHS |

|           |                            |          |      |
|-----------|----------------------------|----------|------|
| 30807-484 | Front Panel without Handle | 40.3 mm  | RoHS |
| 30807-481 | Front Panel without Handle | 20 mm    | RoHS |
| 30807-778 | Front Panel without Handle | 20 mm    | RoHS |
| 30807-777 | Front Panel without Handle | 25 mm    | RoHS |
| 30807-779 | Front Panel without Handle | 40.3 mm  | RoHS |
| 30807-752 | Front Panel without Handle | 30.1 mm  | RoHS |
| 30807-780 | Front Panel without Handle | 80.9 mm  | RoHS |
| 30807-766 | Front Panel without Handle | 141.9 mm | RoHS |
| 30807-758 | Front Panel without Handle | 70.8 mm  | RoHS |
| 30807-757 | Front Panel without Handle | 106.3 mm | RoHS |
| 30807-755 | Front Panel without Handle | 60.6 mm  | RoHS |
| 30807-753 | Front Panel without Handle | 50.5 mm  | RoHS |
| 30807-833 | Front Panel without Handle | 35.2 mm  | RoHS |

## ADDITIONAL PRODUCT DETAILS

---

Please order fixing material (sleeves, collar screws) separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**