nVent | SCHROFF

We connect and protect

15 PCB-Tainer

CATALOG NUMBER

15B-7-3

The Series 15 PCB Tainer is ideal for PCB retention within low shock and vibration applications.

WARNING: This product can expose you to chemicals including beryllium, which is known to the State of California to cause cancer. For more information, go to www.P65Warnings.ca.gov.

CERTIFICATIONS

DFARS Compliant

FEATURES

- Available unplated or with silver, copper, gold, nickel, zinc clear chromate, or zinc yellow chromate plating
- Constructed from beryllium copper or stainless steel
- Weight 0.63 g/cm (0.056 oz/")
- For sheet metal applications
- Mounts to the enclosure with standard rivets, eyelets or screws
- Height 4.35 mm (0.171")
- Width 12.7 mm (0.50")
- Length 50.8 mm (2.0") to 254.0 mm (10.0"), 12.7 mm (0.5") increments
- Spring based retention design
- Supports PCB thickness of 1.59 mm (0.063")
- Mounting hole Ø 2.77 +0.03\-0.08 (Ø 0.109 + 0.001\- 0.003)

PRODUCT ATTRIBUTES

- Product Type: PCB Retainer
- Material: Stainless Steel; Beryllium Copper
- Type: PCB Tainer (Spring Design)

ADDITIONAL PRODUCT DETAILS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including beryllium, which is known to the State of California to cause cancer. For more information, go to www.P65Warnings.ca.gov.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.