

LE260 Extracting Lever Actuated Card-Lok

CATALOG NUMBER

LE260-4.80TM2-2



The Series LE260 features a tool-free lever design, ideal for field level maintenance, as well as an integrated extraction providing a 4:1 mechanical advantage. Shipped pre-calibrated for clamp force on request.

⚠ **WARNING:** This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

CERTIFICATIONS



FEATURES

Length 96.5 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

Integrated extractor

DSCC CID 59789

5 segment, shafted design

Lever actuated

Weight 1.17 g/cm (0.105 oz/')

Flexible mounting options

Min expansion 8.26 mm (0.325")

Profile 6.35 mm (0.250") x 6.26 mm (0.270")

Available with black anodized plating only

For cold wall applications

Average clamp force = pre-calibrated to 125 lbs or 145 lbs, customer defined

PRODUCT ATTRIBUTES

Product Type: PCB Retainer
Material: Aluminum
Type: Shafted
Thermal Performance: Good
Profile: 6.35 x 6.26 mm
Clamp Force: 45 – 90kgf
Gap Width: PCB + (7.0 - 7.9 mm)

ADDITIONAL PRODUCT DETAILS

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	+971.4.378.1700
Chat with us:	Betschdorf, France	Qingdao, China	Bangalore, India
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	+91.80.6715.2001
	Warsaw, Poland	Singapore	Istanbul, Turkey
	+48.22.209.98.35	+65.6768.5800	+90.216.250.7374
	Assago, Italy	Shin-Yokohama, Japan	Chat with us:
	+39.02.932.7141	+81.45.476.0271	nvent.com/schroff
	Chat with us:	Chat with us:	
	nvent.com/schroff	nvent.com/schroff	



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE