

# **EER Trapezoidal Deck Hanger**



## **CERTIFICATIONS**



### **FEATURES**

Supports wire from decking


## **SPECIFICATIONS**

Table 1/2									
Catalog Number	Article Number	E-Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)			
EER	171470	1341098	Spring Steel	nVent CADDY Armour	0.8 - 3 mm	6.8 mm			

Table 2/2									
Catalog Number	Article Number	E-Number	Drill Bit Diameter	Static Load 1 (F1)	Static Load 2 (F2)				
EER	171470	1341098	7mm	450N	900N				

## **ADDITIONAL PRODUCT DETAILS**

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

## Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

