

MTSB Spring Toggle with Nut/Washer



FEATURES

Washer, nut and toggle included

For fixing into hollow walls, hollow ceilings and suspended ceilings

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Rod Size (RS)	Length (L)
MTSB4	584410	1305112	Steel	Electrogalvanized	4	90mm

Table 2/2


Catalog Number	Article Number	E-Number	Drill Bit Diameter	Ultimate Static Load (F)
MTSB4	584410	1305112	14mm	1750N

ADDITIONAL PRODUCT DETAILS

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.

Spring toggle requires a minimum clearance of 35 mm (1.38") to open when installed.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

