


nVent CADDY EZ Riser



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

CERTIFICATIONS



FEATURES

Only one tool needed to tighten due to serrated wash-heads

Installs up to 60% faster than standard riser clamps

Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily

No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	Hole Size (HS)	A	B
EZR0050	179225		21.3 mm	9.9 mm	215.9 mm	130.2 mm

CatalogNumber	Article Number	E-Number	Outer Diameter (OD)	Hole Size (HS)	A	B
EZR0075	179226		26.7 mm	9.9 mm	228.6 mm	136.5 mm
EZR0100	179227		33.4 mm	9.9 mm	228.6 mm	142.9 mm
EZR0125	179228		42.2 mm	9.9 mm	241.3 mm	152.4 mm
EZR0150	179229		48.3 mm	9.9 mm	250.8 mm	158.8 mm
EZR0200	179230		60.3 mm	9.9 mm	260.4 mm	177.8 mm
EZR0250	179231	3533404	73 mm	9.9 mm	279.4 mm	190.5 mm
EZR0300	179232	3533405	88.9 mm	9.9 mm	298.5 mm	206.4 mm
EZR0350	179233	3533406	101.6 mm	13.2 mm	320.7 mm	238.1 mm
EZR0400	179234	3533407	114.3 mm	13.2 mm	330.2 mm	254 mm
EZR0500	179235		141.3 mm	13.2 mm	368.3 mm	298.5 mm
EZR0600	179236	3533408	168.3 mm	13.2 mm	406.4 mm	323.9 mm

Table 2/2				
Catalog Number	Article Number	E-Number	C	Static Load
EZR0050	179225		22.2 mm	1100N
EZR0075	179226		22.2 mm	1100N
EZR0100	179227		22.2 mm	1100N
EZR0125	179228		22.2 mm	1100N
EZR0150	179229		22.2 mm	1100N
EZR0200	179230		25.4 mm	1100N

Catalog Number	Article Number	E-Number	C	Static Load
EZR0250	179231	3533404	25.4 mm	1735N
EZR0300	179232	3533405	25.4 mm	2400N
EZR0350	179233	3533406	31.8 mm	2980N
EZR0400	179234	3533407	31.8 mm	3600N
EZR0500	179235		38.1 mm	5200N
EZR0600	179236	3533408	38.1 mm	6900N

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

