


Strut to Strut Connector



FEATURES

Consists of two half castings, nut and bolt

Allows for bolting two strut channels back to back through the slots

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	A	B
STS	315450	3435694	Steel	Electrogalvanized	32 mm	25 mm

Table 2/2


Catalog Number	Article Number	E-Number	C	Torque (TQ)	Static Load
STS	315450	3435694	12.7 mm	7 N·m	4900N

ADDITIONAL PRODUCT DETAILS

Minimum of 2 required. Maximum spacing 1 foot (300mm).

Minimum half-slot dimensions 9/16" x 7/8" (14.3 mm x 22.2 mm).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

