


Threaded Rod



FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M101000	592610	3533958	Steel	Electrogalvanized	4.8	M10
050M101000HD	592615	3435974	Steel	Hot-Dip Galvanized	4.8	M10
050M101000S4	592740	3534926	Stainless Steel 304 (EN 1.4301)		70	M10
050M121000	592630	3533965	Steel	Electrogalvanized	4.8	M12
050M121000HD	592635	3435975	Steel	Hot-Dip Galvanized	4.8	M12


CatalogNumber	Article Number	E-Number	Material	Finish	Quality Class	Rod Size (RS)
050M121000S4	592760	3534931	Stainless Steel 304 (EN 1.4301)		70	M12
050M161000	400332	3435866	Steel	Electrogalvaniz ed	4.8	M16
050M61000	592570	3535253	Steel	Electrogalvaniz ed	4.8	M6
050M61000S4	592700		Stainless Steel 304 (EN 1.4301)		70	M6
050M81000	592590	3533952	Steel	Electrogalvaniz ed	4.8	M8
050M81000S4	592720	3534922	Stainless Steel 304 (EN 1.4301)		70	M8
050M102000	592620	3533961	Steel	Electrogalvaniz ed	4.8	M10
050M103000	592670	3533963	Steel	Electrogalvaniz ed	4.8	M10
050M122000	592640	3533967	Steel	Electrogalvaniz ed	4.8	M12
050M123000	592680	3533969	Steel	Electrogalvaniz ed	4.8	M12
050M62000	592580	3535254	Steel	Electrogalvaniz ed	4.8	M6
050M63000	592650	3535255	Steel	Electrogalvaniz ed	4.8	M6
050M82000	592600	3533954	Steel	Electrogalvaniz ed	4.8	M8
050M83000	592660	3533956	Steel	Electrogalvaniz ed	4.8	M8
050M102000S4	592750	3534928	Stainless Steel 304 (EN 1.4301)		70	M10
050M62000S4	592710		Stainless Steel 304 (EN 1.4301)		70	M6
050M82000S4	592730	3534924	Stainless Steel 304 (EN 1.4301)		70	M8

Table 2/2

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M101000	592610	3533958	1000mm	7000N
050M101000HD	592615	3435974	1000mm	7000N
050M101000S4	592740	3534926	1000mm	7000N
050M121000	592630	3533965	1000mm	10000N
050M121000HD	592635	3435975	1000mm	10000N
050M121000S4	592760	3534931	1000mm	10000N
050M161000	400332	3435866	1000mm	18000N
050M61000	592570	3535253	1000mm	2400N
050M61000S4	592700		1000mm	2400N
050M81000	592590	3533952	1000mm	4500N
050M81000S4	592720	3534922	1000mm	4500N
050M102000	592620	3533961	2000mm	7000N
050M103000	592670	3533963	3000mm	7000N
050M122000	592640	3533967	2000mm	10000N
050M123000	592680	3533969	3000mm	10000N
050M62000	592580	3535254	2000mm	2400N
050M63000	592650	3535255	3000mm	2400N
050M82000	592600	3533954	2000mm	4500N

Catalog Number	Article Number	E-Number	Length (L)	Static Load
050M83000	592660	3533956	3000mm	4500N
050M102000S4	592750	3534928	2000mm	7000N
050M62000S4	592710		2000mm	2400N
050M82000S4	592730	3534924	2000mm	4500N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

