

VDF TORX Wood-to-Metal Screw with TORX® Head



FEATURES

Wood dowel screw with metric thread connection

TORX® head

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Screw Diameter (Sc)	Length (L)
VDFM8050	593270	3534108	Steel	Electrogalvanized	8	50mm
VDFM8050S4	400477	3534962	Stainless Steel 304 (EN 1.4301)		8	50mm
VDFM10050	593560	3535298	Steel	Electrogalvanized	10	50mm
VDFM10060	593330	3534119	Steel	Electrogalvanized	10	60mm
VDFM8060	593280	3534111	Steel	Electrogalvanized	8	60mm
VDFM8070	593290	3534113	Steel	Electrogalvanized	8	70mm

CatalogNumber	Article Number	E-Number	Material	Finish	ScrewDiameter (Sc)	Length (L)
VDFM10080	593340	3534122	Steel	Electrogalvaniz ed	10	80mm
VDFM10100	593350	3534124	Steel	Electrogalvaniz ed	10	100mm
VDFM12120	400403	3435881	Steel	Electrogalvaniz ed	12	120mm
VDFM8080	593300	3534115	Steel	Electrogalvaniz ed	8	80mm
VDFM8080S4	400478	3534964	Stainless Steel 304 (EN 1.4301)		8	80mm
VDFM8100	593310	3534117	Steel	Electrogalvaniz ed	8	100mm
VDFM10100S4	400482	3534963	Stainless Steel 304 (EN 1.4301)		10	100mm
VDFM8150	593410	3535294	Steel	Electrogalvaniz ed	8	150mm
VDFM10120	593370	3534128	Steel	Electrogalvaniz ed	10	120mm
VDFM10150	593570	3535299	Steel	Electrogalvaniz ed	10	150mm
VDFM8120	593400	3535293	Steel	Electrogalvaniz ed	8	120mm
VDFM8200	593420	3535295	Steel	Electrogalvaniz ed	8	200mm

Table 2/2

Catalog Number	Article Number	E-Number	A	C	TORX®
VDFM8050	593270	3534108	40 mm	10 mm	T25
VDFM8050S4	400477	3534962	28 mm	15 mm	T25
VDFM10050	593560	3535298	30 mm	18 mm	T25
VDFM10060	593330	3534119	30 mm	18 mm	T25


Catalog Number	Article Number	E-Number	A	C	TORX®
VDFM8060	593280	3534111	30 mm	20 mm	T25
VDFM8070	593290	3534113	30 mm	25 mm	T25
VDFM10080	593340	3534122	40 mm	30 mm	T25
VDFM10100	593350	3534124	60 mm	30 mm	T25
VDFM12120	400403	3435881	55 mm	30 mm	T30
VDFM8080	593300	3534115	40 mm	30 mm	T25
VDFM8080S4	400478	3534964	40 mm	30 mm	T25
VDFM8100	593310	3534117	40 mm	40 mm	T25
VDFM10100S4	400482	3534963	55 mm	40 mm	T25
VDFM8150	593410	3535294	45 mm	50 mm	T25
VDFM10120	593370	3534128	60 mm	50 mm	T25
VDFM10150	593570	3535299	60 mm	50 mm	T25
VDFM8120	593400	3535293	50 mm	50 mm	T25
VDFM8200	593420	3535295	50 mm	50 mm	T25

ADDITIONAL PRODUCT DETAILS

No HEX when length is 50.0 mm.

No TORX® head with the stainless steel screws.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

