

Ground Mounted Plinth, PGM



Cables can be easily routed through the ground plinth, which is mounted underground, allowing cables to be channelled and therefore, wired more quickly.

FEATURES

Description: Ground mounted plinth 1000 mm height. Excavation depth: 700-950 mm.

Material: 2 mm galvanized steel.

Finish: RAL 7035 polyester powder coated.

Pack quantity: 1 kit of ground mounted plinth.

SPECIFICATIONS

Thickness: 2mm
Finish: Galvanized
Material: Galvanized Steel
Color: Light Gray
Color Code: RAL 7035

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
PGM10064	2411860	1000mm	600mm	400mm	Aluminum	Free-Standing
PGM10066	2411861	1000mm	600mm	600mm	Aluminum	Free-Standing
PGM10084	2411862	1000mm	800mm	400mm	Aluminum	Free-Standing
PGM10086	2411863	1000mm	800mm	600mm	Aluminum	Free-Standing
PGM10124	2411864	1000mm	1200mm	400mm	Aluminum	Free-Standing
PGM10126	2411865	1000mm	1200mm	600mm	Aluminum	Free-Standing
PGM10184	2411866	1000mm	1800mm	400mm	Aluminum	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE