

## Mounting Angles (19-inch), DNN



19" equipment can be easily fitted in consoles, either in the factory or in the field, when these profiles are used.

### FEATURES

---

Description: To achieve 19" or partial 19" in 800 mm wide enclosures, these profiles can be mounted with the mounting brackets DNB. To achieve 19" in 600 mm wide enclosures, use the brackets DND.

Material: 2 mm zinc plated steel.

Pack quantity: 2 pieces.

SPECIFICATIONS

**Thickness:** 2mm  
**Material:** Steel  
**Finish:** Zinc Plated

| Table 1/1      |        |       |       |            |                                |            |
|----------------|--------|-------|-------|------------|--------------------------------|------------|
| Catalog Number | Height | Width | Depth | Rack Units | Enclosure Material             | Quick Ship |
| DNN06          | 267mm  | 45mm  | 49mm  | 6U         | Mild Steel,<br>Stainless Steel | No         |
| DNN09          | 400mm  | 45mm  | 49mm  | 9U         | Mild Steel,<br>Stainless Steel | No         |
| DNN10          | 445mm  | 45mm  | 49mm  | 10U        | Mild Steel,<br>Stainless Steel | No         |
| DNN11          | 489mm  | 45mm  | 49mm  | 11U        | Mild Steel,<br>Stainless Steel | No         |
| DNN13          | 579mm  | 45mm  | 49mm  | 13U        | Mild Steel,<br>Stainless Steel | No         |
| DNN15          | 667mm  | 45mm  | 49mm  | 15U        | Mild Steel,<br>Stainless Steel | No         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE