

Mounting Plates Wall Mounted Enclosures, AMP



The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.

FEATURES

Description: Steel mounting plate for wall mounted enclosures. All sizes from 800 mm and above are strengthened by folded edges. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Galvanized steel.

Pack quantity: 1 piece.

SPECIFICATIONS

Thickness: 2mm
Finish: Galvanized
Material: Mild Steel

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Panel Size	Enclosure Material
AMP02020	2414321	200mm	199mm	2mm	170 x 150mm	Mild Steel
AMP02520	2414322	250mm	199mm	2mm	220 x 150mm	Mild Steel
AMP02525	2414323	250mm	249mm	2mm	220 x 200mm	Mild Steel
AMP03025	2414324	300mm	249mm	2mm	270 x 200mm	Mild Steel
AMP03030	2414325	300mm	299mm	2mm	270 x 250mm	Mild Steel
AMP03040		300mm	400mm	2mm	270 x 350mm	Mild Steel
AMP03060	2414326	300mm	599mm	2mm	270 x 550mm	Mild Steel
AMP03080	2414327	300mm	799mm	2mm	270 x 750mm	Mild Steel
AMP03525	2414330	350mm	249mm	2mm	320 x 200mm	Mild Steel
AMP04030	2414331	400mm	299mm	2mm	370 x 250mm	Mild Steel
AMP04040	2414332	400mm	400mm	2mm	370 x 350mm	Mild Steel
AMP04050	2414333	400mm	500mm	2mm	370 x 450mm	Mild Steel
AMP04060	2414334	400mm	599mm	2mm	370 x 550mm	Mild Steel
AMP05030	2414335	500mm	299mm	2mm	470 x 250mm	Mild Steel
AMP05040	2414336	500mm	350mm	2mm	470 x 350mm	Mild Steel
AMP05050	2414337	500mm	500mm	2mm	470 x 450mm	Mild Steel

Catalog Number	E-Number	Height	Width	Depth	Panel Size	EnclosureMaterial
AMP06040	2414338	600mm	400mm	2mm	570 x 350mm	Mild Steel
AMP06050	2414339	600mm	500mm	2mm	570 x 450mm	Mild Steel
AMP06060	2414340	600mm	599mm	2mm	570 x 550mm	Mild Steel
AMP06080	2414341	600mm	799mm	2mm	570 x 750mm	Mild Steel
AMP07050	2414342	700mm	500mm	2mm	670 x 450mm	Mild Steel
AMP10100	2414351	1000mm	999mm	12mm	970 x 950mm	Mild Steel
AMP10120	2410976	1000mm	1199mm	12mm	970 x 950mm	Mild Steel
AMP12120	2414355	1200mm	1199mm	12mm	1170 x 1150mm	Mild Steel
AMP03100	2414328	300mm	999mm	12mm	270 x 950mm	Mild Steel
AMP03120	2414329	300mm	1199mm	12mm	270 x 1150mm	Mild Steel
AMP08040	2414343	800mm	400mm	12mm	770 x 350mm	Mild Steel
AMP08060	2414344	800mm	599mm	12mm	770 x 550mm	Mild Steel
AMP08080	2414345	800mm	799mm	12mm	770 x 750mm	Mild Steel
AMP08120	2414347	800mm	1199mm	12mm	770 x 1150mm	Mild Steel
AMP10060	2414349	1000mm	599mm	12mm	970 x 550mm	Mild Steel
AMP10080	2414350	1000mm	799mm	12mm	970 x 750mm	Mild Steel
AMP12060	2414352	1200mm	599mm	12mm	1170 x 550mm	Mild Steel
AMP12080	2414353	1200mm	799mm	12mm	1170 x 750mm	Mild Steel
AMP12100	2414354	1200mm	999mm	12mm	1170 x 950mm	Mild Steel
AMP14100	2414356	1400mm	999mm	12mm	1370 x 950mm	Mild Steel

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE