

IceStop Self-Regulating Cable Kit



nVent RAYCHEM IceStop self-regulating trace heating cable kits provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES

Simple to design

Easy to install, pre-terminated kits: 5 - 30 m, each with 8 m power cable, GM-RAKE fixing bracket and RayClic end seal

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Nominal Height:	6 mm
Cold Lead Length:	8 m
Nominal Width:	14 mm
Nominal Power Output, In Air @ 0°C, 230V:	18 W/m
Nominal Power Output, In Ice Water @ 0°C, 230V:	36 W/m
Max Continuous Exposure Temperature, Power On:	65 °C
Max Intermittent Exposure Temperature, Power On:	85 °C
Nominal Cable Weight:	120 g/m
Supply Voltage:	220 – 240 V
Max Cumulative Hours for Intermittent Exposure:	800 h
Min Installation Temperature:	-18 °C
Color:	Black
Ground Path Type:	Braid
Outer Jacket Material:	Modified Polyolefin
Heating Cable Technology:	Self-Regulating

Table 1/1

Catalog Number	Item Name	E-Number	Length
----------------	-----------	----------	--------

106160-000	GM-2X-SA-8	1038241	8 m
159067-000	GM-2X-SA-12	1038242	12 m
191808-000	GM-2X-SA-5	1038240	5 m
650854-000	GM-2X-SA-16	1038243	16 m
838627-000	GM-2X-SA-25	1038245	25 m
925956-000	GM-2X-SA-30	1038246	30 m
973923-000	GM-2X-SA-20	1038244	20 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT