

Telescopic Slide, Universal, Heavy Load, 2 U



Telescopic slides with 10 to 100 kg load capacity, > 100% extension length and with lateral mounting capability on 19". Robust telescopic sliding-rails - suitable for the installation of 19 inch chassis are suitable for mounting server enclosures from our product portfolio. Due to the extremely robust construction and high load capacity, the telescopic slides can also be used with very heavy housings.

CERTIFICATIONS



FEATURES

Static load-carrying capacity per pair 72 - 100 kg

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

End stop damped

Extension length > 100 %

Rail width k = 19.1 mm, max. installation width of extension/drawer w = 411 mm

SPECIFICATIONS

- Material:** Steel
- Product Type:** Telescopic Slide
- Finish:** Zinc Plated

Table 1/1

Catalog Number	Length	Package Quantity	Static Load	Type	Quick Ship
20110-190	300mm	2	77kg	Universal	No

Catalog Number	Length	Package Quantity	Static Load	Type	Quick Ship
20110-198	700mm	2	72kg	Universal	No
20110-196	600mm	2	88kg	Universal	No
20110-195	550mm	2	94kg	Universal	No
20110-194	500mm	2	100kg	Universal	No
20110-191	350mm	2	83kg	Universal	No
20110-193	450mm	2	94kg	Universal	No
20110-192	400mm	2	88kg	Universal	No

ADDITIONAL PRODUCT DETAILS

To mount on 19" plane please order assembly kit separately.

Universal telescopic rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE