

nVent CADDY Speed Link SLK with Y-Toggle



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and two pre-assembled toggle end fittings

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

SPECIFICATIONS

Table 1/2


| Catalog Number | Article Number | Material | Finish | Static Load Safety Factor | Complies With | Wire Rope Diameter |
|----------------|----------------|----------------------------------|-------------------|---------------------------|-----------------|--------------------|
| SLK2Y300L2 | 196552 | Steel, Zinc Alloy, Polypropylene | Electrogalvanized | 5:1 | SMACNA HVAC-DCS | 2 mm |

Table 2/2

| Catalog Number | Article Number | Wire Rope Length | Wire Rope "Y" Length (YL) | A | B | Static Load |
|----------------|----------------|------------------|---------------------------|-------|------|-------------|
| SLK2Y300L2 | 196552 | 2m | 0.3m | 42 mm | 8 mm | 440N |

Thickness (T): 12.5 mm
Width (W): 19 mm
Height (H): 55 mm
Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

