

PNG Loop Hanger for PVC Pipe



FEATURES

Suspends variable pipe services

SPECIFICATIONS

Finish: Polyester


Material: Steel

Color: White

Table 1/1								
Catalog Number	Outer Diameter (OD)	Rod Size (RS)	A	В	С	Static Load		
PNG040PVCPP C	43 mm	M10	78 mm	52 mm	30.5 mm	1500N		
PNG050PVCPP C	55 mm	M10	96 mm	63 mm	34.5 mm	1500N		
PNG065PVCPP C	69 mm	M10	111 mm	71.5 mm	36.5 mm	1500N		
PNG080PVCPP C	82 mm	M12	131 mm	82.5 mm	41 mm	1500N		

CatalogNumber	Outer Diameter (OD)	Rod Size (RS)	A	В	С	Static Load
PNG100PVCPP C	110 mm	M12	170 mm	108 mm	52.5 mm	1500N
PNG150PVCPP C	160 mm	M12	230 mm	155 mm	74.5 mm	1500N
PNG225PVCPP C	250 mm	M12	391 mm	255 mm	129 mm	6000N
PNG300PVCPP C	315 mm	M12	493 mm	325 mm	167 mm	7500N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

