

# Basic PDU, EB0311-A, 230 VAC, 1-PH, 16 A

## Data Solutions

### CATALOG NUMBER

**EB0311-A**



Modular, compact PDU. Ultra-Low Profile Design

### FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (12) C13

Socket Quantity: 12

Color: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 0

Input Cable Location: Front Feed

Input Voltage: 100 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Output Voltage: 100 – 240VAC

Amperage (Derated Amperage): 16 A

Plug Type: C20

Rack Units: 1U

Removable Input Cable: Yes

Metering Type: None

Package Quantity: 1

Input Cable Length: 0m

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**