

Ground Rod and Clip Kit



FEATURES

Ground rod with 99.9% pure electrolytic copper coating

Ground rod has a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Ground rod is 12mm diameter, 254 um copper coating thickness and 1350 mm long to meet AS3000 requirement (min. 1200mm buried underground)

SPECIFICATIONS

Table 1/1

Catalog Number	Rod Length	Ground Rod Diameter, Actual	Complies With	Unit Weight
611240TC	1350mm	12 mm	IEC® EN 62561-2	13.73 kg

ADDITIONAL PRODUCT DETAILS

Kit includes: 10 copper-bonded ground rods (611240A), 10 ground rod clips (EAD1), 10 tags (TAG30X50) packaged inside of a tube.

AS3000 require rods with minimum diameter of 12mm and minimum copper coating of 250 um.

AS3000 require rods to be buried at least 1200mm. 611240TC rod is 1350mm long to allow extra length for wire connection.

611240TC rod is not applicable for UL listing (UL® 467 requires GR to be at least 8' (2.44m) in length).

IEC® EN 62561-2 supercedes EN 50164-2.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE