

Ground Rod Clamp, U-Bolt, One Conductor, Parallel



FEATURES

Accepts conductor in parallel orientation only


Fits 16 mm² and 25 mm² conductors when the backplate is reversed to the flat side

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Conductor Size	Unit Weight
REC16120	Copper Alloy, Stainless Steel 304 (EN 1.4301)	1/2" - 5/8"	12.7 - 15.9 mm	#4 Solid - 4/0 Stranded, 16 mm ² Stranded - 120 mm ² Stranded	0.41 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE