

Through Roof PVC Upper Connection



CERTIFICATIONS



FEATURES

Allows for lightning protection conductors to be concealed in ceiling or walls

Attaches to existing through roof PVC pipe

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/2

Catalog Number	Material	Finish	Connection Material, In-Line Conductor	Connection Material, Parallel Conductor	Height (H)	Outer Diameter (OD)
LPA664	Aluminum, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Bare	Aluminum	Aluminum	136.8 mm	33.4 mm

CatalogNumber	Material	Finish	Connection Material, In- Line Conductor	Connection Material, Parallel Conductor	Height (H)	Outer Diameter (OD)
LPC664A	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Bare	Copper	Aluminum	136.8 mm	33.4 mm
LPC664BI	Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Bare	Copper	Bi-Metallic	136.8 mm	33.4 mm
LPC664L	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Tinned	Tinned Copper	Tinned Copper	136.8 mm	33.4 mm
LPC664	Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305)	Bare	Copper	Copper	136.8 mm	33.4 mm


Table 2/2

Catalog Number	Unit Weight
LPA664	0.17 kg
LPC664A	0.3 kg
LPC664BI	0.37 kg
LPC664L	0.45 kg
LPC664	0.45 kg

ADDITIONAL PRODUCT DETAILS

Always consult the roof manufacturer or owner for proper flashing materials.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including vinyl chloride, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE