

# A30S4E Free-Stand Single and Dual Access Enclosure



This single-door enclosure provides industry-leading protection for systems incorporating large components or complex mounting configurations in highly corrosive environments. The addition of 19-in. rack-mounting accessories makes these enclosures ideal for providing rugged protection for sensitive rack-mounted components in harsh industrial environments. The enclosure is typically used in food-processing plants, pharmaceutical manufacturing facilities, petrochemical plants and waste-water treatment facilities.

## INDUSTRY STANDARDS

IEC EN 60529, IP66

IEC EN 50102, IK10

IEC EN 62208;

UL 508A Listed;

Type 4, 4X, 12 File No. E61997

NEMA Type 4, 4X, 12

## FEATURES

Two-door enclosures are provided with a removable centerpost for easy mounting plate installation

Seamless foam-in-place polyurethane gasket assures a water-tight and dust-tight seal

High-impact thermoplastic data pocket provided with each enclosure

Base plinth 100 mm included, with front and rear removable cover for easy cable entry

External surface body and door brushed finish grain 240, Ra less than or equal to 0,8 um, smooth internal surface (2B)

Heavy-duty three-point latching mechanism operated by Type 316L stainless steel PowerGlide padlocking handle

Seams continuously welded and ground smooth

Body grounding, studs door and body

Bottom gland plates, 3,0 mm removable from inside, with grounding stud

Door opening angle 100 degrees

## SPECIFICATIONS

|                                 |         |
|---------------------------------|---------|
| <b>Thickness:</b>               | 2.5mm   |
| <b>Finish:</b>                  | Brushed |
| <b>Mounting Plate Included:</b> | No      |
| <b>Gland Plate Included:</b>    | YES     |

Table 1/1

| Catalog Number | Height | Width  | Depth | Material             | Mounting Plate Height | Mounting Plate Width |
|----------------|--------|--------|-------|----------------------|-----------------------|----------------------|
| A18104SS6FS    | 1800mm | 1000mm | 400mm | Stainless Steel 316L | 1595mm                | 897mm                |
| A18104SSFS     | 1800mm | 1000mm | 400mm | Stainless Steel 304  | 1595mm                | 897mm                |
| A18106SSFS     | 1800mm | 1000mm | 600mm | Stainless Steel 304  | 1595mm                | 897mm                |
| A18124SSFS     | 1800mm | 1200mm | 400mm | Stainless Steel 304  | 1595mm                | 1097mm               |
| A18126SSFS     | 1800mm | 1200mm | 600mm | Stainless Steel 304  | 1595mm                | 1097mm               |
| A1864SSFS      | 1800mm | 600mm  | 400mm | Stainless Steel 304  | 1595mm                | 497mm                |
| A1866SSFS      | 1800mm | 600mm  | 600mm | Stainless Steel 304  | 1595mm                | 497mm                |
| A1884SSFS      | 1800mm | 800mm  | 400mm | Stainless Steel 304  | 1595mm                | 697mm                |
| A1886SSFS      | 1800mm | 800mm  | 600mm | Stainless Steel 304  | 1595mm                | 897mm                |
| A20106SSFS     | 2000mm | 1000mm | 600mm | Stainless Steel 304  | 1795mm                | 897mm                |
| A20108SS6FSDA  | 2000mm | 1000mm | 800mm | Stainless Steel 316L | 1795mm                | 897mm                |
| A20108SSFS     | 2000mm | 1000mm | 800mm | Stainless Steel 304  | 1795mm                | 897mm                |
| A20126SSFS     | 2000mm | 1200mm | 600mm | Stainless Steel 304  | 1795mm                | 1097mm               |
| A20128SS6FSDA  | 2000mm | 1200mm | 800mm | Stainless Steel 316L | 1795mm                | 1097mm               |
| A20128SSFS     | 2000mm | 1200mm | 800mm | Stainless Steel 304  | 1795mm                | 1097mm               |
| A20128SSFSDA   | 2000mm | 1200mm | 800mm | Stainless Steel 304  | 1795mm                | 1097mm               |

| Catalog Number | Height | Width  | Depth | Material             | Mounting Plate Height | Mounting Plate Width |
|----------------|--------|--------|-------|----------------------|-----------------------|----------------------|
| A20168SS6FSDAD | 2000mm | 1560mm | 800mm | Stainless Steel 316L | 1795mm                | 1463mm               |
| A20168SSFSD    | 2000mm | 1560mm | 800mm | Stainless Steel 304  | 1795mm                | 1463mm               |
| A20168SSFSDAD  | 2000mm | 1560mm | 800mm | Stainless Steel 304  | 1795mm                | 1463mm               |
| A2066SSFS      | 2000mm | 600mm  | 600mm | Stainless Steel 304  | 1795mm                | 497mm                |
| A2068SSFS      | 2000mm | 600mm  | 800mm | Stainless Steel 304  | 1795mm                | 497mm                |
| A2086SSFS      | 2000mm | 800mm  | 600mm | Stainless Steel 304  | 1795mm                | 697mm                |
| A2088SS6FS     | 2000mm | 800mm  | 800mm | Stainless Steel 316L | 1795mm                | 697mm                |
| A2088SS6FSDA   | 2000mm | 800mm  | 800mm | Stainless Steel 316L | 1795mm                | 697mm                |
| A2088SSFS      | 2000mm | 800mm  | 800mm | Stainless Steel 304  | 1795mm                | 697mm                |
| A2088SSFSDA    | 2000mm | 800mm  | 800mm | Stainless Steel 304  | 1795mm                | 697mm                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**