

# P14 Position Coupler, Stainless Steel



Stainless steel couplers are specified whenever corrosive environmental conditions combine with the need for high load-bearing strength. nVent LENTON stainless steel couplers are commonly used when the construction materials may come into contact with de-icing salts, salt water or marine environments. Typical applications include bridges and bridge decks.

## FEATURES

Designed to splice the same diameter bars

Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is free to move in its axial direction

Duplex 2205 stainless steel provides a unique combination of strength and corrosion resistance

## SPECIFICATIONS

Table 1/3

| Catalog Number | Material                                      | Finish | Coupler Adjustment | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada |
|----------------|-----------------------------------------------|--------|--------------------|--------------------|----------------|--------------------|
| EL20P14LSSN    | Stainless Steel<br>Duplex 2205<br>(EN 1.4462) | Plain  | Standard           | 20 mm              | #6             | 20M                |

Table 2/3

| Catalog Number | Diameter (Ø) | Length 1 (L1) | Length 2 (L2) | Bar Depth (BD) | Bar Gap 1 (BG1) | Bar Gap 2 (BG2) |
|----------------|--------------|---------------|---------------|----------------|-----------------|-----------------|
| EL20P14LSSN    | 35 mm        | 152 mm        | 163 mm        | 35mm           | 82mm            | 93mm            |

Table 3/3

| Catalog Number | Coupler Body (CB) | Unit Weight |
|----------------|-------------------|-------------|
| EL20P14LSSN    | 76mm              | 0.36 kg     |


**Designed to Meet:**

AASHTO;ABNT NBR 8548:1984;ACI 318 Type 1 (125% Specified Yield);ACI 318 Type 2 (Specified Tensile);ACI 349;ACI 359;AS3600

ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

|                          |                 |                  |                      |
|--------------------------|-----------------|------------------|----------------------|
| <b>North America</b>     | <b>Europe</b>   | <b>Europe</b>    | <b>APAC</b>          |
| +1.800.753.9221          | Netherlands:    | Germany:         | Shanghai:            |
| Option 1 – Customer Care | +31 800-0200135 | 800 1890272      | + 86 21 2412 1618/19 |
| Option 2 – Technical     | France:         | Other Countries: | Sydney:              |
| Support                  | +33 800 901 793 | +31 13 5835404   | +61 2 9751 8500      |



Our powerful portfolio of brands:

CADDYERICOHOFFMANILSCOSCHROFFTRACHTE