

Varistar CP IP 55 Cabinet



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP20 and IP55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Type of protection IP 55

Doors with 3-point locking and screw-fixed side panels

Static load-carrying capacity 1600 kg

Side and rear panels can be installed by one person

EN45545-2 fire safety Gaskets

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Cabinet
Protection Rating:	IP55
Cladding Color Code:	RAL 7021
Frame Material:	Steel

Table 1/3

Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-042	42U	2000mm	Black Grey	600mm	RAL 7021	Steel
10630-041	42U	2000mm	Black Grey	600mm	RAL 7021	Steel

Table 2/3

Catalog Number	Depth	Cladding Color	Type	Package Quantity	Complies With	Finish
----------------	-------	----------------	------	------------------	---------------	--------

10630-042	600mm	Black Grey	Steel Door, Plain	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	Powder Coated
10630-041	600mm	Black Grey	Steel Door, Glazed	1	IEC 60529, IEC 61587-1, IEC 60297-3-100	Powder Coated

Table 3/3

Catalog Number	Material	Quick Ship
10630-042	Steel	No
10630-041	Steel	No

ADDITIONAL PRODUCT DETAILS

Further dimensions and versions available on ServicePLUS IP 55. Please order base/plinth separately. For the assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE