


Strut Channel Type C, Slotted, Steel, Hot-dip galv., 3m x 21mm x 41mm x 2.5mm

CATALOG NUMBER

C25H3000HD



CERTIFICATIONS



FEATURES

Cold formed channel, slotted

Strut channels for medium to heavy applications

For individual fastening or for efficiently constructing pipe or tube routes

PRODUCT ATTRIBUTES

Article Number: 310281

Strut Type: C (21 x 41 mm)

Material: Steel

Finish: Hot-Dip Galvanized

Thickness (T): 2.5 mm

Length (L): 3000mm

Height (H): 21 mm

Width (W): 41 mm

A: 26 mm

B: 13 mm

C: 27 mm

D: 50 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

