We connect and protect

Rail Web Mold Clamp, Adjustable, T20 Welder Style, 89 mm Mold Size, 600 mm Max Jaw Opening

Data Solutions

CATALOG NUMBER

PBC105P

FEATURES

- Adjusts for a wide span of uses including frogs and switches
- Lightweight and easy to use
- Can also be used on standard (single) rail
- SBC105RR provides improved safety with non-sharp profiles and reflecting tape for high visiblity

PRODUCT ATTRIBUTES

- Welder Style: T20
- Mold Size: 89 mm
- Jaw Opening: 600mm max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.