

# Hol-Sealers Non-Metallic Hole Seal

Designed for use in corrosive environments to seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water. These hole seals are suitable for sealing enclosure openings in industries such as petroleum and chemical processing, wastewater processing, pulp and paper, outdoor monitoring and any other industry exposed to harsh environments.

## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66



## FEATURES

Innovative 3-in-1 self-centering design reduces inventory requirements; 3 models cover 9 common industry cutouts ranging from 1/2 inch (13mm) to 2-1/2 inch (64mm)

Non-metallic construction provides superior corrosion resistance for reliability in harsh environments

UV stabilized; ideal for direct sunlight (avoids fiberbloom associated with fiberglass)

Chemically resistant to a broad range of chemicals

Durable and impact resistant; resists cracking

Sold in quantities of 2 per catalog number

Cost-effective alternative to stainless steel

Polyester material has a UL 94 rating of 5VA

Easy to install; no tools required

Thread and nut are constructed of non-glass-filled polyester

Oil-resistant gasket included

SPECIFICATIONS

| Table 1/1      |                |               |           |          |            |            |
|----------------|----------------|---------------|-----------|----------|------------|------------|
| Catalog Number | Article Number | Hole Diameter | Material  | Finish   | Color      | Color Code |
| ASPB05075NM    | 16307          | 33mm max      | Polyester | Textured | Light Gray | RAL 7035   |
| AS150200250NM  | 16311          | 80mm max      | Polyester | Textured | Light Gray | RAL 7035   |
| ASPB100125NM   | 16308          | 49mm max      | Polyester | Textured | Light Gray | RAL 7035   |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE