


19" Fan Unit, 1 U

Power Utilities

Fan Unit for installation into a 1U space within the Cabinet.



CERTIFICATIONS



FEATURES

Mechanical strain relief for mains cables

Can be adapted to sub racks

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage AC	Input Voltage DC
10713-100	230 V min	
10713-102	115 V min	
10713-104	230 V min	

Catalog Number	Input Voltage AC	Input Voltage DC
10713-106	115 V min	
10713-103		24 V min
10713-107		24 V min

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE