

# Novastar Cabinet Without Door and Rear Panel

## Power Utilities



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

### CERTIFICATIONS



### FEATURES

Static load-carrying capacity up to 400 kg (see specification table)

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Colors: RAL 7021 or color combination RAL 7021/ RAL 7035

Bolted, die-cast frame with Al extrusions

Without door and rear panel

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Frame Color | Height | Frame Color Code | Cladding Material | Width |
|----------------|-------------|-------------|--------|------------------|-------------------|-------|
|----------------|-------------|-------------|--------|------------------|-------------------|-------|

|           |      |            |         |          |       |        |
|-----------|------|------------|---------|----------|-------|--------|
| 15230-001 | 9 U  | Black Grey | 456 mm  | RAL 7021 | Steel | 553 mm |
| 16230-001 | 9 U  | Black Grey | 456 mm  | RAL 7021 | Steel | 553 mm |
| 15230-002 | 12 U | Black Grey | 589 mm  | RAL 7021 | Steel | 553 mm |
| 15230-003 | 12 U | Black Grey | 589 mm  | RAL 7021 | Steel | 553 mm |
| 16230-002 | 12 U | Black Grey | 589 mm  | RAL 7021 | Steel | 553 mm |
| 16230-003 | 12 U | Black Grey | 589 mm  | RAL 7021 | Steel | 553 mm |
| 15230-004 | 16 U | Black Grey | 767 mm  | RAL 7021 | Steel | 553 mm |
| 15230-005 | 16 U | Black Grey | 767 mm  | RAL 7021 | Steel | 553 mm |
| 16230-004 | 16 U | Black Grey | 767 mm  | RAL 7021 | Steel | 553 mm |
| 16230-005 | 16 U | Black Grey | 767 mm  | RAL 7021 | Steel | 553 mm |
| 15230-006 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 15230-007 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 15230-008 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 16230-006 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 16230-007 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 16230-008 | 20 U | Black Grey | 945 mm  | RAL 7021 | Steel | 553 mm |
| 15230-009 | 25 U | Black Grey | 1167 mm | RAL 7021 | Steel | 553 mm |
| 15230-010 | 25 U | Black Grey | 1167 mm | RAL 7021 | Steel | 553 mm |
| 16230-009 | 25 U | Black Grey | 1167 mm | RAL 7021 | Steel | 553 mm |

|           |      |            |         |          |       |        |
|-----------|------|------------|---------|----------|-------|--------|
| 16230-010 | 25 U | Black Grey | 1167 mm | RAL 7021 | Steel | 553 mm |
| 15230-011 | 34 U | Black Grey | 1567 mm | RAL 7021 | Steel | 553 mm |
| 15230-012 | 34 U | Black Grey | 1567 mm | RAL 7021 | Steel | 553 mm |
| 16230-011 | 34 U | Black Grey | 1567 mm | RAL 7021 | Steel | 553 mm |
| 16230-012 | 34 U | Black Grey | 1567 mm | RAL 7021 | Steel | 553 mm |
| 15230-013 | 38 U | Black Grey | 1745 mm | RAL 7021 | Steel | 553 mm |
| 15230-014 | 38 U | Black Grey | 1745 mm | RAL 7021 | Steel | 553 mm |
| 16230-013 | 38 U | Black Grey | 1745 mm | RAL 7021 | Steel | 553 mm |
| 16230-014 | 38 U | Black Grey | 1745 mm | RAL 7021 | Steel | 553 mm |
| 15230-015 | 43 U | Black Grey | 1967 mm | RAL 7021 | Steel | 553 mm |
| 15230-016 | 43 U | Black Grey | 1967 mm | RAL 7021 | Steel | 553 mm |
| 16230-015 | 43 U | Black Grey | 1967 mm | RAL 7021 | Steel | 553 mm |
| 16230-016 | 43 U | Black Grey | 1967 mm | RAL 7021 | Steel | 553 mm |
| 15230-017 | 47 U | Black Grey | 2145 mm | RAL 7021 | Steel | 553 mm |
| 15230-018 | 47 U | Black Grey | 2145 mm | RAL 7021 | Steel | 553 mm |
| 16230-017 | 47 U | Black Grey | 2145 mm | RAL 7021 | Steel | 553 mm |
| 16230-018 | 47 U | Black Grey | 2145 mm | RAL 7021 | Steel | 553 mm |

Table 2/3

| Catalog Number | Cladding Color | Depth | Static Load | Cladding Color Code | Complies With | Frame Material |
|----------------|----------------|-------|-------------|---------------------|---------------|----------------|
|----------------|----------------|-------|-------------|---------------------|---------------|----------------|

|           |            |        |         |          |                 |          |
|-----------|------------|--------|---------|----------|-----------------|----------|
| 15230-001 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-001 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-002 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-003 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-002 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-003 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-004 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-005 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-004 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-005 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-006 | Black Grey | 500 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-007 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-008 | Black Grey | 800 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-006 | Light Grey | 500 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-007 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-008 | Light Grey | 800 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-009 | Black Grey | 600 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-010 | Black Grey | 800 mm | 200 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-009 | Light Grey | 600 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |

|           |            |        |         |          |                 |          |
|-----------|------------|--------|---------|----------|-----------------|----------|
| 16230-010 | Light Grey | 800 mm | 200 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-011 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-012 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-011 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-012 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-013 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-014 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-013 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-014 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-015 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-016 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-015 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-016 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 15230-017 | Black Grey | 600 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 15230-018 | Black Grey | 800 mm | 400 kgf | RAL 7021 | IEC 60297-3-100 | Aluminum |
| 16230-017 | Light Grey | 600 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |
| 16230-018 | Light Grey | 800 mm | 400 kgf | RAL 7035 | IEC 60297-3-100 | Aluminum |

Table 3/3

| Catalog Number | Product Type |
|----------------|--------------|
| 15230-001      | Cabinet      |

| Catalog Number | Product Type |
|----------------|--------------|
| 16230-001      | Cabinet      |
| 15230-002      | Cabinet      |
| 15230-003      | Cabinet      |
| 16230-002      | Cabinet      |
| 16230-003      | Cabinet      |
| 15230-004      | Cabinet      |
| 15230-005      | Cabinet      |
| 16230-004      | Cabinet      |
| 16230-005      | Cabinet      |
| 15230-006      | Cabinet      |
| 15230-007      | Cabinet      |
| 15230-008      | Cabinet      |
| 16230-006      | Cabinet      |
| 16230-007      | Cabinet      |
| 16230-008      | Cabinet      |
| 15230-009      | Cabinet      |
| 15230-010      | Cabinet      |
| 16230-009      | Cabinet      |

| Catalog Number | Product Type |
|----------------|--------------|
| 16230-010      | Cabinet      |
| 15230-011      | Cabinet      |
| 15230-012      | Cabinet      |
| 16230-011      | Cabinet      |
| 16230-012      | Cabinet      |
| 15230-013      | Cabinet      |
| 15230-014      | Cabinet      |
| 16230-013      | Cabinet      |
| 16230-014      | Cabinet      |
| 15230-015      | Cabinet      |
| 15230-016      | Cabinet      |
| 16230-015      | Cabinet      |
| 16230-016      | Cabinet      |
| 15230-017      | Cabinet      |
| 15230-018      | Cabinet      |
| 16230-017      | Cabinet      |
| 16230-018      | Cabinet      |

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**