

## Front Panel, Flat, Unshielded, D-Sub Cutouts



Flat front panel with cutout for D-Sub connectors.  
Unshielded version.

## CERTIFICATIONS



## FEATURES

Non-shielded version

Al, 2.5 mm, front anodized, rear conductive

## SPECIFICATIONS

|                        |                            |
|------------------------|----------------------------|
| <b>Rack Height:</b>    | 3U                         |
| <b>Rack Width:</b>     | 4HP                        |
| <b>Material:</b>       | Aluminum                   |
| <b>Finish:</b>         | Anodized; Passivated       |
| <b>Accessory Type:</b> | Front panel                |
| <b>Product Type:</b>   | Front Panel                |
| <b>Type:</b>           | Front Panel without Handle |

Table 1/2

| Catalog Number | Package Quantity | Mounting       | Front Finish | Rear Finish | Number of Pins | Treated Edges |
|----------------|------------------|----------------|--------------|-------------|----------------|---------------|
| 30118-341      | 1                | Screw-on Front | Anodized     | Conductive  | (3) 9          | No            |
| 30118-342      | 1                | Screw-on Front | Anodized     | Conductive  | (1) 15         | No            |
| 30118-343      | 1                | Screw-on Front | Anodized     | Conductive  | (1) 25         | No            |
| 30118-344      | 1                | Screw-on Front | Anodized     | Conductive  | (2) 9          | No            |
| 30118-345      | 1                | Screw-on Front | Anodized     | Conductive  | (2) 15         | No            |
| 30118-346      | 1                | Screw-on Front | Anodized     | Conductive  | (2) 25         | No            |
| 30118-347      | 1                | Screw-on Front | Anodized     | Conductive  | (3) 9          | No            |

Table 2/2

| Catalog Number | Complies With                   | Depth (D) | EMC Shielding | Height (H) | Width (W) | Quick Ship |
|----------------|---------------------------------|-----------|---------------|------------|-----------|------------|
| 30118-341      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-342      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-343      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-344      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-345      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-346      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |
| 30118-347      | IEC 60297-3-101, IEEE 1101.1/10 | 2.5mm     | No            | 128.4mm    | 19.98mm   | No         |

ADDITIONAL PRODUCT DETAILS


Delivery is in standard pack multiples. Pricing is per individual item.

Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

DIAGRAMS





### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

#### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:

[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**