

517 Parallel Cable Connector



CERTIFICATIONS





FEATURES

Cable splice with positive two bolt tension grip on cable or wire


For use with all full size cables on Class I/II structures


Listed to UL® 96

SPECIFICATIONS

Conductor Size, UL: Class 1 - Class 2 (4/0 Max)

Table 1/1					
Catalog Number	Material	Finish	Depth (D)	Width (W)	Unit Weight
LPA517	Aluminum		48.51mm	42.16 mm	0.11 kg
LPC517L	Copper	Tinned	48.51mm	42.16 mm	0.23 kg
LPC517	Copper		48.51mm	42.16 mm	0.23 kg





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF