

# Compression Sleeve



## FEATURES

Tin plated for corrosion prevention

Annealed copper eases the crimping operation

Contains a positive stop for proper positioning of the cables inside the sleeve

## SPECIFICATIONS

**Material:** Copper

**Finish:** Tinned


Table 1/1

Catalog Number	Conductor Size	Length (L)	Tool/Die Type
A2314J	#9 Solid	36.5mm	SBT031DJ Manual Compression Tool/No die required
A2363J	#6 Solid	36.5mm	SBT031DJ Manual Compression Tool/No die required
A2364J	#8 Solid	36.5mm	SBT031DJ Manual Compression Tool/No die required
A2367J	3/16" Stranded	36.5mm	SBT031DJ Manual Compression Tool/No die required

ADDITIONAL PRODUCT DETAILS

Note: Each sleeve accommodates 3/16" Bondstrand in one end. The other end of the sleeve accommodates the conductor sizes indicated in the above table.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE