

Copper-Bonded Ground Rod, Two Pigtails



FEATURES

Assembly for use on wooden utility poles

Anti-copper theft application

Conductors exothermically welded to ground rod with nVent ERICO Cadweld, then the connection is covered with heat shrink wrap

Complete assembly covered in black insulation

SPECIFICATIONS


Table 1/2

Catalog Number	Material	Tensile Strength	Insulated	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Length 1 (L1)
615800CW0505	Copper-Bonded Steel	552 kPa Min	Yes	5/8"	14.2 mm	3.05 m

Table 2/2

Catalog Number	Length 2 (L2)	Plating Thickness	Conductor Size	Unit Weight
615800CW0505	0.5 m	254µm	70 mm ²	4.7 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE