

# Panel 19-inch Bottom-Hinged



Hinged panel pivots to 90 degrees with positive stop, providing a stable platform for punch-down interconnects. Thumbscrews secure the panel in the upright position. Integral Velcro® cable tiedown slots facilitate cable routing. Cover protects equipment and cables. Shipped fully assembled. Velcro® is a trademark of Velcro Industries B.V.

## INDUSTRY STANDARDS

---

UL 2416 Listed; File No. E230874

cUL CSA C22.2 No. 182.4 Listed, File No. E230874

EIA 310-D

## FEATURES

---

Hinged panel pivots to 90 degrees with positive stop, providing a stable platform for punch-down interconnects

Thumbscrews secure the panel in the upright position

Integral Velcro® cable tiedown slots facilitate cable routing

Cover protects equipment and cables

Shipped fully assembled

## SPECIFICATIONS

---

**Color:** Jet Black  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Body Thickness	Door Thickness
E19BHPM8U12	11011	356mm	508mm	305mm	1.5mm	2.7mm
E19BHPM6U12	11008	267mm	508mm	305mm	1.5mm	2.7mm
E19BHPM4U12	11007	203mm	508mm	305mm	1.5mm	2.7mm

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**